

BC916KC1-10 Cut Sheet



Minerallac hammer-on beam clamp conduit hanger assembly, spring clip, bottom mount, 75 lbs, UL Type UL 2239. Package of 10. For use with 9/16 to 3/4in flanges and 1in conduit.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BC916KC1-10>

Technical Specifications

Brand	Minerallac	Rigid Metallic Conduit (RMC) Trade Size	1in
Item	Conduit hanger assembly	Electrical Metallic Tubing (EMT) Trade Size	1in
Mount Type	Hammer-on beam clamp	Intermediate Metallic Conduit (IMC) Trade Size	1in
Hanger Type	Spring clip	Reduced Wall Flexible Metal Conduit Trade Size	3/4in
Mount Side	Bottom	Liquid-tight Flexible Metal Conduit (LFMC) Trade Size	1in
Material	Spring steel	UL Type	UL 2239
Finish	Zinc phosphate plated	Quantity per Pack	10
Mounting Holes	1/4-20 UNC back	For Use With	9/16 to 3/4in flanges and 1in conduit
Minimum Flange Thickness	9/16in		
Maximum Flange Thickness	3/4in		
Load Rating	75 lbs		
Outside Diameter	1.11in-1.31in		

Agency Approvals

UL Listed File #	E165884
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document