

BCM603-2PQ Cut Sheet



Bussmann modular fuse block, accepts CC fuses, 30A, 600V, 2-pole, 18-10 AWG copper only, pressure plate with quick-connect terminals, 35mm DIN rail or panel mount. Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BCM603-2PQ>

Technical Specifications

Brand	Bussmann
Item	Fuse block
Modular	Yes
Blown Fuse Indicator	No
Multi-Wire	No
Accepts Fuse Class	CC
Amperage Rating	30A
Voltage Rating	600V
Number of Poles	2
Conductor Size	18-10 AWG copper only
Conductor Connection Type	Pressure plate with quick-connect terminals
SCCR Rating	200kA SCCR
Fuse Connection Type	Clip with reinforced spring
Mounting	35mm DIN rail or panel
Quantity per Pack	5
Additional Information	Covers sold separately

Agency Approvals

UL Listed File #	E14853
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	47235-6225-01
RoHS Status	No
EU REACH	View EU REACH document
Other	None