

# BCS017K Cut Sheet



Balluff capacitive proximity sensor, tubular, 12mm diameter x 60mm body, stainless steel housing, NPN/PNP, N.O., 5mm sensing distance, flush, 100 Hz switching frequency, IP67, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BCS017K>

## Technical Specifications

<b>Brand</b>	Balluff
<b>Item</b>	Proximity sensor
<b>Sensor Type</b>	Capacitive
<b>Application</b>	Standard duty
<b>Shape</b>	Tubular
<b>Housing Size</b>	12mm diameter x 60mm body
<b>Housing Material</b>	Stainless steel
<b>Barrel Type</b>	Threaded
<b>Adjustable</b>	No
<b>Number of Wires</b>	4
<b>Switching Output</b>	NPN/PNP
<b>Operation Mode</b>	N.O.

<b>Sensing Distance</b>	5mm
<b>Mounting Type</b>	Flush
<b>IO-Link Compatible</b>	No
<b>Switching Frequency</b>	100 Hz
<b>Operating Voltage</b>	12-30 VDC
<b>Operating Temperature</b>	-10 to 80 deg C
<b>Weld Field Immune</b>	No
<b>Chip Immune</b>	No
<b>IP Rating</b>	IP67
<b>Connection</b>	4-pin M12 quick-disconnect
<b>Includes</b>	Mounting hardware
<b>Additional Information</b>	Purchase cable separately

## Agency Approvals

<b>UL Listed File #</b>	E117437
<b>CE</b>	<a href="#">View CE declarations</a>
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/BCS017K.pdf>  
See store item page for other formats.