

BD-24AE-J Cut Sheet



Patlite audible alarm, 90 dB at 1m, 191 Hz to 1.7 kHz tone frequency, (32) selectable tone(s), 12-24 VDC, panel or surface mount, ABS plastic housing, light gray, IP54.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BD-24AE-J>

Technical Specifications

Brand	Patlite
Item	Audible alarm
Loudness Decibel	90 dB at 1m
Tone Frequency	191 Hz to 1.7 kHz
Tone Type	(32) selectable
Touch to Acknowledge	No
Voltage Rating	12-24 VDC
Mounting	Panel or surface
Housing Material	ABS plastic
Color	Light gray
IP Rating	IP54

Agency Approvals

UL Listed File #	None
UL Recognized File #	S24210
UL Hazardous File #	None
CE	View CE declarations
CSA File #	NONE
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document