

BFFC-14N-18N Cut Sheet



NITRA pneumatic threaded fitting, straight, brass body, 1/4in female NPT to 1/8in female NPT. Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BFFC-14N-18N>

Technical Specifications

| | |
|---------------------------|--------------------------------------|
| Brand | NITRA |
| Item | Pneumatic Threaded Fitting |
| Fitting Type | Straight |
| Body Material | Brass |
| Connection | 1/4in female NPT to 1/8in female NPT |
| Operating Pressure | 800 psi |
| Quantity per Pack | 5 |

Agency Approvals

| | |
|-----------------------------|----------------------------------------|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |