


BFFC-14N Cut Sheet



NITRA pneumatic threaded fitting, straight, brass body, brass threads, (1) 1/4in female NPT to (1) 1/4in female NPT. Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BFFC-14N>

Technical Specifications

| | |
|--------------------------|--|
| Brand | NITRA |
| Item | Fitting |
| Working Fluid | Air or inert gas |
| Fitting Connection Type | Threaded |
| Fitting Type | Straight |
| Body Material | Brass |
| Thread Material | Brass |
| Fitting Measurement Type | SAE |
| Connection | (1) 1/4in female NPT to (1) 1/4in female NPT |
| Operating Pressure | 800 psi |
| Operating Temperature | -65 to 250 deg F |
| Quantity per Pack | 5 |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/BFFC-14N.pdf>
See store item page for other formats.