

BFFC-38N Cut Sheet



NITRA pneumatic threaded fitting, straight, brass body, 3/8in female NPT to 3/8in female NPT. Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BFFC-38N>

Technical Specifications

Brand	NITRA
Item	Pneumatic Threaded Fitting
Fitting Type	Straight
Body Material	Brass
Connection	3/8in female NPT to 3/8in female NPT
Operating Pressure	800 psi
Quantity per Pack	5

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document