

# BFR-3233 Cut Sheet



NITRA precision pneumatic filter-regulator, 1/4in female NPT inlet(s), 1/4in female NPT outlet(s), 0-120 psi adjustable range, manual drain, die-cast aluminum bowl, sight gauge.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BFR-3233>

## Technical Specifications

Brand	NITRA
Item	Filter-regulator
Regulator Type	Precision
Working Fluid	Air or inert gas
Inlet Port	1/4in female NPT
Outlet Port	1/4in female NPT
Pressure Range	0-120 psi adjustable
Drain Type	Manual
Bowl Material	Die-cast aluminum
Bowl Guard	No
Sight Gauge	Yes
Includes	Replaceable 40 micron filter element

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/BFR-3233.pdf>  
See store item page for other formats.