

# BFR-3433 Cut Sheet



NITRA precision pneumatic filter-regulator, 1/2in female NPT inlet(s), 1/2in female NPT outlet(s), 0-120 psi adjustable range, manual drain, die-cast aluminum bowl, sight gauge.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BFR-3433>

## Technical Specifications

<b>Brand</b>	NITRA
<b>Item</b>	Filter-regulator
<b>Regulator Type</b>	Precision
<b>Working Fluid</b>	Pneumatic
<b>Inlet Port</b>	1/2in female NPT
<b>Outlet Port</b>	1/2in female NPT
<b>Pressure Range</b>	0-120 psi adjustable
<b>Drain Type</b>	Manual
<b>Bowl Material</b>	Die-cast aluminum
<b>Bowl Guard</b>	No
<b>Sight Gauge</b>	Yes
<b>Includes</b>	Replaceable 40 micron filter element

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>