

# BFRHP-14N Cut Sheet



NITRA pneumatic threaded fitting, recessed hex plug, brass body, brass threads, 1/4in male NPT. Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BFRHP-14N>

## Technical Specifications

<b>Brand</b>	NITRA
<b>Item</b>	Fitting
<b>Working Fluid</b>	Air or inert gas
<b>Fitting Connection Type</b>	Threaded
<b>Fitting Type</b>	Recessed hex plug
<b>Body Material</b>	Brass
<b>Thread Material</b>	Brass
<b>Fitting Measurement Type</b>	SAE
<b>Connection</b>	1/4in male NPT
<b>Operating Pressure</b>	800 psi
<b>Operating Temperature</b>	-65 to 250 deg F
<b>Quantity per Pack</b>	5

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/BFRHP-14N.pdf>  
See store item page for other formats.