

BFRHP-38N Cut Sheet



NITRA pneumatic threaded fitting, recessed hex plug, brass body, brass threads, 3/8in male NPT. Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BFRHP-38N>

Technical Specifications

Brand	NITRA
Item	Fitting
Working Fluid	Air or inert gas
Fitting Connection Type	Threaded
Fitting Type	Recessed hex plug
Body Material	Brass
Thread Material	Brass
Connection	3/8in male NPT
Operating Pressure	800 psi
Operating Temperature	-65 to 250 deg F
Quantity per Pack	5

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/BFRHP-38N.pdf>
See store item page for other formats.