

BFSE-14N Cut Sheet



NITRA pneumatic threaded fitting, street elbow, brass body, brass threads, 1/4in female NPT to 1/4 male NPT. Package of 2.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BFSE-14N>

Technical Specifications

Brand	NITRA
Item	Fitting
Working Fluid	Air or inert gas
Fitting Connection Type	Threaded
Fitting Type	Street elbow
Body Material	Brass
Thread Material	Brass
Connection	1/4in female NPT and 1/4 male NPT
Operating Pressure	800 psi
Operating Temperature	-65 to 250 deg F
Quantity per Pack	2

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/BFSE-14N.pdf>
See store item page for other formats.