

BH20599 Cut Sheet



Bondhus ProGuard L-key hex key set, external hex, 22 pieces, 6.8in (173mm) overall length, protanium high torque steel, metric and imperial, stubby and ball-end tip.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BH20599>

Technical Specifications

Brand	Bondhus
Series	ProGuard
Item	Hex key set
Number of Pieces	22
Wrench Type	L-key
Measurement Type	Metric and imperial
Material	Protanium high torque steel
Insulated	No
Overall Length	6.8in (173mm)

Tip Type	External hex
Ratcheting	No
Wrench Features	Stubby and ball-end tip
Set Includes	Includes (13) imperial stubby double ball-end L-key hex keys (0.050in, 1/16in, 5/64in, 3/32in, 7/64in, 1/8in, 9/64in, 5/32in, 3/16in, 7/32in, 1/4in, 5/16in, 3/8in), (9) metric stubby double ball-end L-key hex keys (1.5mm, 2mm, 2.5mm, 3mm, 4mm, 5mm, 6mm, 8mm, 10mm), (2) wear-resistant tool holders
Application	Screwdriving

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document