

BH22199 Cut Sheet



Bondhus ProGuard L-key hex key set, external hex, 22 pieces, 6.8in (173mm) overall length, protanium high torque steel, metric and imperial.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BH22199>

Technical Specifications

Brand	Bondhus
Series	ProGuard
Item	Hex key set
Number of Pieces	22
Wrench Type	L-key
Measurement Type	Metric and imperial
Material	Protanium high torque steel
Insulated	No
Overall Length	6.8in (173mm)

Tip Type	External hex
Ratcheting	No
Set Includes	Includes (13) imperial long L-key hex keys (0.050in, 1/16in, 5/64in, 3/32in, 7/64in, 1/8in, 9/64in, 5/32in, 3/16in, 7/32in, 1/4in, 5/16in, 3/8in), (9) metric long L-key hex keys (1.5mm, 2mm, 2.5mm, 3mm, 4mm, 5mm, 6mm, 8mm, 10mm), (2) wear-resistant tool holders
Application	Screwdriving

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document