

BH67037 Cut Sheet

Bondhus ProGuard L-key hex key set, external hex, 13 pieces, 7.8in (198mm) overall length, protanium high torque steel, imperial, stubby and double ball-end tip.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BH67037>

Technical Specifications

Brand	Bondhus
Series	ProGuard
Item	Hex key set
Number of Pieces	13
Wrench Type	L-key
Measurement Type	Imperial
Material	Protanium high torque steel
Insulated	No
Overall Length	7.8in (198mm)

Tip Type	External hex
Ratcheting	No
Wrench Features	Stubby and double ball-end tip
Set Includes	Includes (13) MaxTorque stubby ball-end L-key hex keys (0.050in, 1/16in, 5/64in, 3/32in, 7/64in, 1/8in, 9/64in, 5/32in, 3/16in, 7/32in, 1/4in, 5/16in, 3/8in), (1) wear-resistant clip
Application	Screwdriving

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document