

BL82-221A Cut Sheet



Norgren Excelon Plus 82 pneumatic combination unit, filter-regulator-lubricator, 1/4in female NPT inlet(s), 1/4in female NPT outlet(s), 4-145 psi range, polycarbonate bowl, manual drain, manual shutoff valve.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BL82-221A>

Technical Specifications

| | |
|----------------|---|
| Brand | Norgren |
| Working Fluid | Air |
| Series | Excelon Plus 82 |
| Item | Combination filter-regulator-lubricator |
| Inlet Port | 1/4in female NPT |
| Outlet Port | 1/4in female NPT |
| Pressure Range | 4-145 psi |
| Bowl Material | Polycarbonate |

| | |
|----------------------|--|
| Drain Type | Manual |
| Manual Shutoff Valve | Yes |
| Padlockable | Yes |
| Soft Start Valve | No |
| Pressure Switch | No |
| Includes | Integral pressure gauge and replaceable 40 micron filter element |

Agency Approvals

| | |
|----------------------|---|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/BL82-221A.pdf>
See store item page for other formats.