

BM-202H Cut Sheet



Patlite audible alarm buzzer, 85 dB at 1m, 3.9 kHz to 4.6 kHz tone frequency, (2) selectable tone(s), 24 VAC/VDC, 30mm, panel mount, ABS plastic housing, black, IP30.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BM-202H>

Technical Specifications

| | |
|-----------------------------|----------------------|
| Brand | Patlite |
| Item | Audible alarm buzzer |
| Loudness Decibel | 85 dB at 1m |
| Tone Frequency | 3.9 kHz to 4.6 kHz |
| Tone Type | (2) selectable |
| Touch to Acknowledge | No |
| Voltage Rating | 24 VAC/VDC |
| Barrel Size | 30mm |
| Mounting | Panel |
| Housing Material | ABS plastic |
| Color | Black |
| IP Rating | IP30 |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | NONE |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |