

# BM-202H Cut Sheet



Patlite audible alarm buzzer, 85 dB at 1m, 3.9 kHz to 4.6 kHz tone frequency, (2) selectable tone(s), 24 VAC/VDC, 30mm, panel mount, ABS plastic housing, black, IP30.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BM-202H>

## Technical Specifications

<b>Brand</b>	Patlite
<b>Item</b>	Audible alarm buzzer
<b>Loudness Decibel</b>	85 dB at 1m
<b>Tone Frequency</b>	3.9 kHz to 4.6 kHz
<b>Tone Type</b>	(2) selectable
<b>Touch to Acknowledge</b>	No
<b>Number of Alarms</b>	2
<b>Voltage Rating</b>	24 VAC/VDC
<b>Barrel Size</b>	30mm
<b>Mounting</b>	Panel
<b>Housing Material</b>	ABS plastic
<b>Color</b>	Black
<b>IP Rating</b>	IP30

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	NONE
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/BM-202H.pdf>  
See store item page for other formats.