

BM-212H Cut Sheet



Patlite audible alarm buzzer, 90 dB at 1m, 3.9 kHz to 4.6 kHz tone frequency, (2) selectable tone(s), 120 VAC, 30mm, panel mount, ABS plastic housing, black, IP30.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BM-212H>

Technical Specifications

Brand	Patlite
Item	Audible alarm buzzer
Loudness Decibel	90 dB at 1m
Tone Frequency	3.9 kHz to 4.6 kHz
Tone Type	(2) selectable
Touch to Acknowledge	No
Voltage Rating	120 VAC
Barrel Size	30mm
Mounting	Panel
Housing Material	ABS plastic
Color	Black
IP Rating	IP30

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	NONE
RoHS Status	No
EU REACH	View EU REACH document