



Mounting head nylon 6.6 cable tie, 4in length, 0.09in width, 18 lb tensile strength, 0.86in maximum bundle diameter, natural. Package of 100.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BM-H1125>

---

## Technical Specifications

<b>Item</b>	Cable tie
<b>Cable Tie Type</b>	Mounting head
<b>Material</b>	Nylon 6.6
<b>Length</b>	4in
<b>Width</b>	0.09in
<b>Tensile Strength</b>	18 lb
<b>Maximum Bundle Diameter</b>	0.86in
<b>Color</b>	Natural
<b>Quantity per Pack</b>	100

---

## Agency Approvals

<b>UL Listed File #</b>	E223175
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>