



Mounting head nylon 6.6 cable tie, 8in length, 0.18in width, 50 lb tensile strength, 1.9in maximum bundle diameter, natural. Package of 100.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BM-H2048>

Technical Specifications

Item	Cable tie
Cable Tie Type	Mounting head
Material	Nylon 6.6
Length	8in
Width	0.18in
Tensile Strength	50 lb
Maximum Bundle Diameter	1.9in
Color	Natural
Quantity per Pack	100

Agency Approvals

UL Listed File #	E223175
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document