



Lashing nylon 6.6 cable tie, 40in length, 0.49in width, 250 lb tensile strength, 11.61in maximum bundle diameter, black. Package of 100.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BM-N1012>

Technical Specifications

Item	Cable tie
Cable Tie Type	Lashing
Material	Nylon 6.6
Length	40in
Width	0.49in
Tensile Strength	250 lb
Maximum Bundle Diameter	11.61in
Color	Black
Quantity per Pack	100

Agency Approvals

UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document