

BM-N1025 Cut Sheet

Nylon 6.6 cable tie, 4in length, 0.09in width, 18 lb tensile strength, 0.7in maximum bundle diameter, black. Package of 100.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BM-N1025>

Technical Specifications

Item	Cable tie
Material	Nylon 6.6
Length	4in
Width	0.09in
Tensile Strength	18 lb
Maximum Bundle Diameter	0.7in
Color	Black
Quantity per Pack	100

Agency Approvals

UL Listed File #	E223175
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document