



UV resistant nylon 12 cable tie, 7in length, 0.35in width, 79 lb tensile strength, 1.69in maximum bundle diameter, black. Package of 100.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BM-N1890>

---

## Technical Specifications

<b>Item</b>	Cable tie
<b>Cable Tie Type</b>	UV resistant
<b>Material</b>	Nylon 12
<b>Length</b>	7in
<b>Width</b>	0.35in
<b>Tensile Strength</b>	79 lb
<b>Maximum Bundle Diameter</b>	1.69in
<b>Color</b>	Black
<b>Quantity per Pack</b>	100

---

## Agency Approvals

<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>