

# BM-N2936M Cut Sheet



Nylon 6.6 cable tie, 11in length, 0.14in width, 40 lb tensile strength, 2.99in maximum bundle diameter, black. Package of 1000.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BM-N2936M>

---

## Technical Specifications

|                                |           |
|--------------------------------|-----------|
| <b>Item</b>                    | Cable tie |
| <b>Material</b>                | Nylon 6.6 |
| <b>Length</b>                  | 11in      |
| <b>Width</b>                   | 0.14in    |
| <b>Tensile Strength</b>        | 40 lb     |
| <b>Maximum Bundle Diameter</b> | 2.99in    |
| <b>Color</b>                   | Black     |
| <b>Quantity per Pack</b>       | 1000      |

---

## Agency Approvals

|                             |                                        |
|-----------------------------|----------------------------------------|
| <b>UL Listed File #</b>     | E223175                                |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |