



UV resistant nylon 12 cable tie, 14in length, 0.35in width, 112 lb tensile strength, 3.66in maximum bundle diameter, black. Package of 100.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BM-N3690>

Technical Specifications

Item	Cable tie
Cable Tie Type	UV resistant
Material	Nylon 12
Length	14in
Width	0.35in
Tensile Strength	112 lb
Maximum Bundle Diameter	3.66in
Color	Black
Quantity per Pack	100

Agency Approvals

UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document