



Releasable nylon 6.6 cable tie, 12in length, 0.29in width, 50 lb tensile strength, 3.15in maximum bundle diameter, natural. Package of 100.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BM-R3076>

Technical Specifications

| | |
|--------------------------------|------------|
| Item | Cable tie |
| Cable Tie Type | Releasable |
| Material | Nylon 6.6 |
| Length | 12in |
| Width | 0.29in |
| Tensile Strength | 50 lb |
| Maximum Bundle Diameter | 3.15in |
| Color | Natural |
| Quantity per Pack | 100 |

Agency Approvals

| | |
|-----------------------------|----------------------------------------|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |