

BM-T22025 Cut Sheet



Identification nylon 6.6 cable tie, 8in length, 0.09in width, 18 lb tensile strength, 1.9in maximum bundle diameter, natural, (1) 1 x 0.31in bottom mounted transversal ID tag. Package of 100.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BM-T22025>

Technical Specifications

Item	Cable tie
Cable Tie Type	Identification
Material	Nylon 6.6
Length	8in
Width	0.09in
Tensile Strength	18 lb
Maximum Bundle Diameter	1.9in
Color	Natural
Marker Type	(1) 1 x 0.31in bottom mounted transversal ID tag
Quantity per Pack	100

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document