

# BM3VHB-016 Cut Sheet



Fuji Electric BM3V series manual motor protector, rotary, 16A, thermal overload, 11.0-16.0A adjustable, 208A instantaneous trip rating, open, 55mm frame.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BM3VHB-016>

## Technical Specifications

<b>Brand</b>	Fuji Electric	<b>Power Poles</b>	(3) N.O.
<b>Series</b>	BM3V	<b>Trip Class</b>	Trip Class 10
<b>Item</b>	Motor protector	<b>Phase Loss Sensitive</b>	Yes
<b>Starter Type</b>	Manual	<b>Ground Fault Protection</b>	No
<b>Actuator Type</b>	Rotary	<b>SCCR Rating</b>	50kA SCCR
<b>Amperage Rating</b>	16A	<b>UL Rating</b>	UL 508 rated
<b>Voltage Rating</b>	600 VAC	<b>Enclosure Type</b>	Open
<b>Horsepower Rating</b>	10hp	<b>Frame</b>	55mm
<b>Relay Type</b>	Thermal overload	<b>Mounting</b>	35mm DIN rail
<b>Operation Type</b>	Bi-metallic	<b>Connection</b>	Screw terminal
<b>Full Load Amperage Range</b>	11.0-16.0A adjustable	<b>Additional Information</b>	For UL Type E listing, Short Circuit Alarm contact block BZ0TKUAB must be added to the MMS. Suitable as a motor disconnect
<b>Instantaneous Trip Rating</b>	208A		
<b>Number of Poles</b>	3		

## Agency Approvals

<b>UL Listed File #</b>	E211710
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>