

BMBCX-E6 Cut Sheet



Bimbed cable gland, M50 x 1.5mm thread type, nickel-plated brass, accepts 27 to 38mm diameter cable, IP68. Package of 2. Mounting hardware included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BMBCX-E6>

Technical Specifications

Brand	Bimbed
Item	Cable gland
Thread Type	M50 x 1.5mm
Material	Nickel-plated brass
Cable OD Range	27 to 38mm
IP Rating	IP68
Strain Relief	No
Quantity per Pack	2
Includes	Mounting hardware

Agency Approvals

UL Listed File #	E199260
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	190896
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/BMBCX-E6.pdf>
See store item page for other formats.