

BMM603-1PQ-1 Cut Sheet



Bussmann modular fuse block, accepts Midget fuses, 30A, 600V, 1-pole, 18-10 AWG copper only, pressure plate with quick-connect terminals, 35mm DIN rail or panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BMM603-1PQ-1>

Technical Specifications

Brand	Bussmann
Item	Fuse block
Modular	Yes
Blown Fuse Indicator	No
Multi-Wire	No
Accepts Fuse Class	Midget
Amperage Rating	30A
Voltage Rating	600V
Number of Poles	1
Conductor Size	18-10 AWG copper only
Conductor Connection Type	Pressure plate with quick-connect terminals
SCCR Rating	200kA SCCR
Fuse Connection Type	Clip with reinforced spring
Mounting	35mm DIN rail or panel
Additional Information	Covers sold separately

Agency Approvals

UL Listed File #	None
UL Recognized File #	E14853
UL Hazardous File #	None
CE	View CE declarations
CSA File #	47235-6225-02
RoHS Status	No
EU REACH	View EU REACH document
Other	None