

BN4040403SS Cut Sheet



Wiegmann enclosure, NEMA 4/4X/12/13, 4 x 4 x 3in (HxWxD), wall mount, 304 stainless steel, No. 3 intermediate polished finish, lift-off cover, (4) stainless steel clamps.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BN4040403SS>

Technical Specifications

Brand	Wiegmann
Item	Enclosure
Slope Top	No
3-Piece Assembly	No
Vented	No
NEMA Rating	4/4X/12/13
IP Rating	IP66
Nominal Enclosure Dimensions	4 x 4 x 3in (HxWxD)
Enclosure Height	4.31in
Enclosure Width	4.31in
Enclosure Depth	3.31in
Mounting	Wall

Integral Mounting Feet	No
Integral Mounting Flange	Yes
Dual Access	No
Knockouts	No
Bottom Gland Plate	No
Material	304 stainless steel
Finish	No. 3 intermediate polished
Cover Type	Lift-off cover
Latch Type	(4) stainless steel clamps
Shelf	No
Padlockable	No
Keylocking	No

Agency Approvals

UL Listed File #	E23553, E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/BN4040403SS.pdf>
See store item page for other formats.