

BN4100804CHSS Cut Sheet



Wiegmann enclosure, NEMA 4/4X/12/13, 10 x 8 x 4in (HxWxD), wall mount, 304 stainless steel, No. 3 intermediate polished finish, single-door, (2) stainless steel clamps.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BN4100804CHSS>

Technical Specifications

Brand	Wiegmann	Integral Mounting Flange	Yes
Item	Enclosure	Dual Access	No
Subpanel	Purchase subpanel separately	Knockouts	No
Slope Top	No	Material	304 stainless steel
NEMA Rating	4/4X/12/13	Finish	No. 3 intermediate polished
IP Rating	IP66	Cover Type	Single-door
Nominal Enclosure Dimensions	10 x 8 x 4in (HxWxD)	Hinge Type	Continuous hinge
Enclosure Height	10.31in	Number of Hinges Per Door	1
Enclosure Width	8.31in	Latch Type	(2) stainless steel clamps
Enclosure Depth	4.34in	Padlockable	No
Mounting	Wall	Keylocking	No
Integral Mounting Feet	No		

Agency Approvals

UL Listed File #	E64791, E6924
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document