

BN4121005CHAL Cut Sheet



Wiegmann enclosure, NEMA 4/4X/12/13, 12 x 10 x 5in (HxWxD), wall mount, 5052-H32 aluminum, No. 3 intermediate polished finish, single-door, (2) stainless steel clamps.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BN4121005CHAL>

Technical Specifications

Brand	Wiegmann
Item	Enclosure
Subpanel	Purchase subpanel separately
Slope Top	No
NEMA Rating	4/4X/12/13
IP Rating	IP66
Nominal Enclosure Dimensions	12 x 10 x 5in (HxWxD)
Enclosure Height	12.31in
Enclosure Width	10.31in
Enclosure Depth	5.14in
Mounting	Wall
Integral Mounting Feet	No

Integral Mounting Flange	Yes
Dual Access	No
Knockouts	No
Material	5052-H32 aluminum
Finish	No. 3 intermediate polished
Cover Type	Single-door
Hinge Type	Continuous hinge
Number of Hinges Per Door	4
Latch Type	(2) stainless steel clamps
Padlockable	No
Keylocking	No

Agency Approvals

UL Listed File #	E64791, E6924
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document