

BN4121010CHQT Cut Sheet



Wiegmann Ultimate Mini-Max series enclosure, NEMA 4/12, 12 x 10 x 10in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, single-door, 1/4-turn semi-flush oil-tight latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BN4121010CHQT>

Technical Specifications

Brand	Wiegmann
Item	Enclosure
Series	Ultimate Mini-Max
Subpanel	Purchase subpanel separately
Slope Top	No
NEMA Rating	4/12
IP Rating	IP66
Nominal Enclosure Dimensions	12 x 10 x 10in (HxWxD)
Enclosure Height	12.31in
Enclosure Width	10.31in
Enclosure Depth	10.75in
Mounting	Wall
Integral Mounting Feet	No

Integral Mounting Flange	Yes
Dual Access	No
Knockouts	No
Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	Single-door
Hinge Type	Concealed hinges
Number of Hinges Per Door	1
Latch Type	1/4-turn semi-flush oil-tight latch
Padlockable	No
Keylocking	No

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document