

BN4121206CHSSA Cut Sheet



Wiegmann enclosure, NEMA 4/4X/12/13, 12 x 12 x 6in (HxWxD), wall mount, 316L stainless steel, No. 3 intermediate polished finish, single-door, (2) stainless steel clamps.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BN4121206CHSSA>

Technical Specifications

Brand	Wiegmann
Item	Enclosure
Subpanel	Purchase subpanel separately
Slope Top	No
NEMA Rating	4/4X/12/13
IP Rating	IP66
Nominal Enclosure Height	12in
Nominal Enclosure Width	12in
Nominal Enclosure Depth	6in
Mounting	Wall
Integral Mounting Feet	No

Integral Mounting Flange	Yes
Dual Access	No
Knockouts	No
Material	316L stainless steel
Finish	No. 3 intermediate polished
Cover Type	Single-door
Hinge Type	Continuous hinge
Number of Hinges Per Door	1
Latch Type	(2) stainless steel clamps
Padlockable	No
Keylocking	No

Agency Approvals

UL Listed File #	E64791, E6924
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/BN4121206CHSSA.pdf>
See store item page for other formats.