# BN4121208CHQTSS Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

Wiegmann Ultimate Mini-Max series enclosure, NEMA 4/4X/12, 12 x 12 x 8in (HxWxD), wall mount, 304 stainless steel, No. 3 intermediate polished finish, single-door, 1/4-turn semi-flush oil-tight latch.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/BN4121208CHQTSS

## Technical Specifications

| | |
|---|---|
| **Brand** | Wiegmann |
| **Item** | Enclosure |
| **Series** | Ultimate Mini-Max |
| **Subpanel** | Purchase subpanel separately |
| **Slope Top** | No |
| **3-Piece Assembly** | No |
| **Vented** | No |
| **NEMA Rating** | 4/4X/12 |
| **IP Rating** | IP66 |
| **Nominal Enclosure Dimensions** | 12 x 12 x 8in (HxWxD) |
| **Enclosure Height** | 12.31in |
| **Enclosure Width** | 12.31in |
| **Enclosure Depth** | 8.75in |
| **Mounting** | Wall |

| | |
|---|---|
| **Integral Mounting Feet** | No |
| **Integral Mounting Flange** | Yes |
| **Dual Access** | No |
| **Knockouts** | No |
| **Bottom Gland Plate** | No |
| **Material** | 304 stainless steel |
| **Finish** | No. 3 intermediate polished |
| **Cover Type** | Single-door |
| **Hinge Type** | Concealed hinges |
| **Number of Hinges Per Door** | 1 |
| **Latch Type** | 1/4-turn semi-flush oil-tight latch |
| **Shelf** | No |
| **Padlockable** | No |
| **Keylocking** | No |

## Agency Approvals

| | |
|---|---|
| **UL Listed File #** | E64791 |
| **UL Recognized File #** | None |
| **UL Hazardous File #** | None |
| **CE** | None |
| **CSA File #** | None |
| **RoHS Status** | No |
| **EU REACH** | View EU REACH document |

## Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/BN4121208CHQTSS.pdf
See store item page for other formats.