

# BN4141206AL Cut Sheet



Wiegmann enclosure, NEMA 4/4X/12/13, 14 x 12 x 6in (HxWxD), wall mount, 5052-H32 aluminum, No. 3 intermediate polished finish, lift-off cover, (8) stainless steel clamps.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BN4141206AL>

## Technical Specifications

<b>Brand</b>	Wiegmann
<b>Item</b>	Enclosure
<b>Subpanel</b>	Purchase subpanel separately
<b>Slope Top</b>	No
<b>3-Piece Assembly</b>	No
<b>Vented</b>	No
<b>NEMA Rating</b>	4/4X/12/13
<b>IP Rating</b>	IP66
<b>Nominal Enclosure Dimensions</b>	14 x 12 x 6in (HxWxD)
<b>Enclosure Height</b>	14.31in
<b>Enclosure Width</b>	12.31in
<b>Enclosure Depth</b>	6.26in
<b>Mounting</b>	Wall

<b>Integral Mounting Feet</b>	No
<b>Integral Mounting Flange</b>	Yes
<b>Dual Access</b>	No
<b>Knockouts</b>	No
<b>Bottom Gland Plate</b>	No
<b>Material</b>	5052-H32 aluminum
<b>Finish</b>	No. 3 intermediate polished
<b>Cover Type</b>	Lift-off cover
<b>Latch Type</b>	(8) stainless steel clamps
<b>Shelf</b>	No
<b>Padlockable</b>	No
<b>Keylocking</b>	No

## Agency Approvals

<b>UL Listed File #</b>	E6924, E23553
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/BN4141206AL.pdf>  
See store item page for other formats.