

BP080A-LF Cut Sheet



Metrol limit switch, precision touch, 8mm diameter, threaded, 1.25mm pitch, 30mm length, 4mm head, stainless steel, ball plunger, 1N contact force, N.O. contact(s), 6.5ft/2m cable length, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BP080A-LF>

Technical Specifications

Brand	Metrol
Item	Limit switch
Switch Type	Precision touch
Diameter	8mm
Barrel Type	Threaded
Length	30mm
Head Type	4mm
Actuator Type	Ball plunger
Contact Force	1N
Contact Type	N.O.
Cable Length	6.5ft/2m
Connection	Pigtail
Conductor Size	26 AWG
Stroke	1.0mm
Repeatability	0.01mm
Thread Pitch	1.25mm
Material	Stainless steel
IP Rating	IP40
Operating Temperature	0 to 80 deg C
Indicating Type	LED indication
Includes	Mounting hardware

Agency Approvals

RoHS Status	No
EU REACH	View EU REACH document