

BP100A-L Cut Sheet



Metrol limit switch, precision touch, 10mm diameter, threaded, 1.5mm pitch, 33mm length, 5mm head, stainless steel, ball plunger, 10-20N contact force, N.O. contact(s), 6.5ft/2m cable length, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BP100A-L>

Technical Specifications

Brand	Metrol
Item	Limit switch
Switch Type	Precision touch
Diameter	10mm
Barrel Type	Threaded
Length	33mm
Head Type	5mm
Actuator Type	Ball plunger
Contact Force	10-20N
Contact Type	N.O.
Cable Length	6.5ft/2m
Connection	Pigtail
Conductor Size	26 AWG
Stroke	1.2mm
Repeatability	0.01mm
Thread Pitch	1.5mm
Material	Stainless steel
IP Rating	IP40
Operating Temperature	0 to 80 deg C
Indicating Type	LED indication
Includes	Mounting hardware

Agency Approvals

RoHS Status	No
EU REACH	View EU REACH document