

# BR-322 Cut Sheet



NITRA precision pneumatic regulator, 1/4in female NPT inlet(s), 1/4in female NPT outlet(s), 0-60 psi adjustable range.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BR-322>

---

## Technical Specifications

|                       |                     |
|-----------------------|---------------------|
| <b>Brand</b>          | NITRA               |
| <b>Item</b>           | Regulator           |
| <b>Regulator Type</b> | Precision           |
| <b>Working Fluid</b>  | Pneumatic           |
| <b>Inlet Port</b>     | 1/4in female NPT    |
| <b>Outlet Port</b>    | 1/4in female NPT    |
| <b>Pressure Range</b> | 0-60 psi adjustable |

---

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | None                                   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |