

# BR-342 Cut Sheet



NITRA precision pneumatic regulator, 1/2in female NPT inlet(s), 1/2in female NPT outlet(s), 0-60 psi adjustable range.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BR-342>

---

## Technical Specifications

<b>Brand</b>	NITRA
<b>Item</b>	Regulator
<b>Regulator Type</b>	Precision
<b>Working Fluid</b>	Pneumatic
<b>Inlet Port</b>	1/2in female NPT
<b>Outlet Port</b>	1/2in female NPT
<b>Pressure Range</b>	0-60 psi adjustable

---

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

---

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/BR-342.pdf>  
See store item page for other formats.