

# BR-342 Cut Sheet



NITRA precision pneumatic regulator, 1/2in female NPT inlet(s), 1/2in female NPT outlet(s), 0-60 psi adjustable range.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BR-342>

## Technical Specifications

Brand	NITRA
Item	Regulator
Regulator Type	Precision
Working Fluid	Air or inert gas
Inlet Port	1/2in female NPT
Outlet Port	1/2in female NPT
Pressure Range	0-60 psi adjustable

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/BR-342.pdf>  
See store item page for other formats.