

BR-N1-250W91 Cut Sheet



Crohms braking resistor, 250W, 91 ohm, NEMA 1, built-in temperature switch. For use with multiple AC drives.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BR-N1-250W91>

Technical Specifications

Brand	Crohms
Item	Braking resistor
Brake Resistor Power Rating	250W
Resistance	91 ohm
Enclosure Type	NEMA 1
Built-in Temperature Switch	Yes
For Use With	Multiple AC drives

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	303117
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/BR-N1-250W91.pdf>
See store item page for other formats.