

# BR-N1-720W50 Cut Sheet



Crohms braking resistor, 720W, 50 ohm, NEMA 1, built-in temperature switch. For use with multiple AC drives.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BR-N1-720W50>

---

## Technical Specifications

<b>Brand</b>	Crohms
<b>Item</b>	Braking resistor
<b>Brake Resistor Power Rating</b>	720W
<b>Resistance</b>	50 ohm
<b>Enclosure Type</b>	NEMA 1
<b>Built-in Temperature Switch</b>	Yes
<b>For Use With</b>	Multiple AC drives

---

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	303117
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

---

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/BR-N1-720W50.pdf>  
See store item page for other formats.