

# BR-N3R-4K7W14P7 Cut Sheet



Crohms braking resistor, 4.7 kW, 14.7 ohm, NEMA 3R, built-in temperature switch. For use with multiple AC drives.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BR-N3R-4K7W14P7>

## Technical Specifications

<b>Brand</b>	Crohms
<b>Item</b>	Braking resistor
<b>Brake Resistor Power Rating</b>	4.7 kW
<b>Resistance</b>	14.7 ohm
<b>Enclosure Type</b>	NEMA 3R
<b>Built-in Temperature Switch</b>	Yes
<b>For Use With</b>	Multiple AC drives

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	303117
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/BR-N3R-4K7W14P7.pdf>  
See store item page for other formats.