


BR-PT-1K2W50 Cut Sheet



Crohm braking resistor, 1.2 kW, 50 ohm, open coil. For use with multiple AC drives.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BR-PT-1K2W50>

Technical Specifications

| | |
|------------------------------------|--------------------|
| Brand | Crohm |
| Item | Braking resistor |
| Brake Resistor Power Rating | 1.2 kW |
| Resistance | 50 ohm |
| Enclosure Type | Open coil |
| Built-in Temperature Switch | No |
| For Use With | Multiple AC drives |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | Certificate 80136215 |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/BR-PT-1K2W50.pdf>
See store item page for other formats.