


BR-PT-1K5W40 Cut Sheet

Crohms braking resistor, 1.5 kW, 40 ohm, open coil. For use with multiple AC drives.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BR-PT-1K5W40>

Technical Specifications

Brand	Crohms
Item	Braking resistor
Brake Resistor Power Rating	1.5 kW
Resistance	40 ohm
Enclosure Type	Open coil
Built-in Temperature Switch	No
For Use With	Multiple AC drives

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	Certificate 80136215
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/BR-PT-1K5W40.pdf>
See store item page for other formats.