

BRY15W33 Cut Sheet



Bryant watertight straight blade connector with cap, 20A, 125 VAC, 1-phase, 2-pole, 3-wire, NEMA 5-20, accepts cord size 0.325-0.625in, UL Type 4, 4X, 6 and 6P, thermoplastic elastomer (PTE) housing, yellow.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BRY15W33>

Technical Specifications

Brand	Bryant
Item	Connector
Application	Watertight
Blade Type	Straight
With Cap	Yes
Amperage Rating	20A
Voltage Rating	125 VAC
Number of Phases	1

Number of Poles	2
Number of Wires	3
Wire Size	18-12 AWG
Configuration	NEMA 5-20
Cord Diameter	0.325-0.625in
UL Type	4, 4X, 6 and 6P
Housing Material	Thermoplastic elastomer (PTE)
Color	Yellow

Agency Approvals

UL Listed File #	E1706
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	1284294
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/BRY15W33.pdf>
See store item page for other formats.