

BRY29W75 Cut Sheet



Bryant watertight locking blade connector with cap, 30A, 250 VAC, 3-phase, 3-pole, 4-wire, NEMA L15-30, accepts cord size 0.385-1.05in, UL Type 4, 4X, 6 and 6P, thermoplastic elastomer (PTE) housing, yellow.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BRY29W75>

Technical Specifications

Brand	Bryant
Item	Connector
Application	Watertight
Blade Type	Locking
With Cap	Yes
Amperage Rating	30A
Voltage Rating	250 VAC
Number of Phases	3

Number of Poles	3
Number of Wires	4
Wire Size	18-10 AWG
Configuration	NEMA L15-30
Cord Diameter	0.385-1.05in
UL Type	4, 4X, 6 and 6P
Housing Material	Thermoplastic elastomer (PTE)
Color	Yellow

Agency Approvals

UL Listed File #	E1706
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	1284294
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/BRY29W75.pdf>
See store item page for other formats.